

# Technical Sheet

## GL OPTI SPHERES


All our spheres connect to any GL spectrometer using a direct connection.

Integrating spheres have become a standard instrument in photometry and radiometry since R. Ulbricht's practical implementation of the light-collecting cubical box more than 115 years ago.

Today, GL Optic produces high reflectance integrating spheres using modern materials such as composite and combining them with the latest calibration technology. They are the optimal solution for luminous flux and radiant power measurement of single LEDs, LED luminaires and modules.

### Features:

- Luminous flux and radiant power measurements
- High reflection BaSO<sub>4</sub> coating with 98 % reflection
- 2π and 4π configurations
- Suitable for compliance with international standards: EN 62471, IESNA LM-79-08, CIE 127:2007, CIE S 025/E:2015 and others



	GL OPTI SPHERE 48	GL OPTI SPHERE 205	GL OPTI SPHERE 500	GL OPTI SPHERE 1000	GL OPTI SPHERE 2000	GL OPTI SPHERE 3000
Application	Luminous flux and radiant power measurement of single LEDs and other small light sources. Mounts directly on spectrometer.	Luminous flux and radiant power measurement of LEDs and other light sources	Luminous flux and radiant power measurement of LED modules and retrofit lamps	Luminous flux and radiant power measurement of large LED modules and luminaires	Luminous flux and radiant power measurement of large LED modules and large luminaires	Radiant power and luminous flux measurements
<b>TECHNICAL DATA</b>						
Spectral range	340 – 1700 nm	340 – 1700 nm	340 – 1700 nm	340 – 1700 nm	340 – 1700 nm	340 – 1700 nm
Sphere inner diameter	48 mm	205 mm	500 mm	1100 mm	2000 mm	3000 mm
Sphere material	Aluminium	Aluminium	Composite	Composite	Carbon steel	Carbon steel
Inner coating	Barium Sulfate (BaSO <sub>4</sub> ) high-reflectance material (R98)	Barium Sulfate (BaSO <sub>4</sub> ) high-reflectance material (R98)	Barium Sulfate (BaSO <sub>4</sub> ) high-reflectance material (R98)	Barium Sulfate (BaSO <sub>4</sub> ) high-reflectance material (R98)	Barium Sulfate (BaSO <sub>4</sub> ) high-reflectance material (R98)	Barium Sulfate (BaSO <sub>4</sub> ) high-reflectance material (R98)
Outer coating	Black textured finish	Black textured finish	Black finish	Black finish	Black textured finish	Grey textured finish

# Technical Sheet

## GL OPTI SPHERES

Reflectance properties	97%	97%	97%	97%	97%	98%
Auxiliary light source	N/A	White LED	White LED	White LED	White LED or halogen	Halogen
Spectrometer port	Direct connection	Direct connection or SMA fiber-optic	Direct connection or SMA fiber-optic	Direct connection or SMA fiber-optic	Direct connection or SMA fiber-optic	Direct connection or SMA fiber-optic
Standards compliance	N/A	CE, LM 79, CIE 127:2007 CIE S 025/E:2015	CE, LM 79, CIE 127:2007 CIE S 025/E:2015	CE, LM 79, CIE 127:2007 CIE S 025/E:2015	CE, LM 79, CIE 127:2007 CIE S 025/E:2015	CE, LM 79, CIE 127:2007 CIE S 025/E:2015
Maximum DUT dimensions in accordance with CIE S 025/E:2015	N/A	20 mm (diameter or diagonal)	50 mm (diameter or diagonal)	100 mm (diameter or diagonal)	200 mm (diameter or diagonal)	300 mm (diameter or diagonal)
Maximum dimension for optimal measurement (1/3 x sphere diameter)	N/A	65 mm (diameter or diagonal)	165 mm (diameter or diagonal)	330 mm (diameter or diagonal)	665 mm (diameter or diagonal)	1000 mm (diameter or diagonal)
Maximum DUT weight	N/A	250 g	3 kg	3 kg	25 kg	25 kg
Sphere frame	N/A	N/A	Hinged	Hinged	Hinged	Hinged with electric powered opening mechanism
Sphere center positioning	N/A	N/A	N/A	N/A	Cross laser mechanism	Cross laser mechanism
Mechanical breadboard with post	N/A	For 4π measurement	For 4π measurement	For 4π measurement	For 4π measurement	For 4π measurement
USB source controller for auxiliary light source	N/A	With current source and relay switch for external power supply	With current source and relay switch for external power supply	With current source and relay switch for external power supply	With current source and relay switch for external power supply	With current source and relay switch for external power supply
Universal post with standard lamp sockets	N/A	N/A	E14, E27, GU10 and G4 for QTH lamp spectral flux source	E14, E27, GU10 and G4 for QTH lamp spectral flux source	E14, E27, GU10 and G4 for QTH lamp spectral flux source	E14, E27, GU10 and G4 for QTH lamp spectral flux source
External dimensions [W x H x D]	52 x 88 x 51 mm	265 x 270 x 225 mm	620 x 760 x 590 mm	1260 x 1800 x 1220 mm	2200 x 2200 x 2300 mm	4200 x 3500 x 3300 mm
Weight	0.126 kg	3.3 kg	17.5 kg	60 kg	200 kg	1100 kg

GL Optic Lichtmesstechnik GmbH | Tobelwasenweg 24 | 73235 Weilheim/Teck | GERMANY  
 Tel.: +49 (0)7023 9504-20 | Fax: +49 (0)7023 9504-830 | office@gloptic.com | www.gloptic.com  
 Geschäftsführer: Michael Gall | Sitz der Gesellschaft: Weilheim/Teck | Amtsgericht Stuttgart HRB746271  
 U-St. IDNR: DE 292228248 | Steuer-Nr.: 69068/56239